



MAXIMUM OPERATING PRESSURE: 200 PSIT.
FLOW RATING: 500-2000 GPM AT 100 PSIT.

WARNING: The electrical control system must incorporate a current limiting circuitry set for a maximum of 3 amps for 12 volts (1.5 amps for 24 volts). Without circuitry set motor may become inoperable if stalled during operation.

Assemble Notes:

- ⚠ Use Parker O-Ring lubricant or equivalent petroleum based lubricant.
- ⚠ Use Loctite 222 or PermaBond 113
- ⚠ Use Low-Temp Lubriplate
- ⚠ Torque to 40 in/lbs.



STYLE 5098
ELECTRICALLY CONTROLLED NOZZLE
WITH MANUAL OVERRIDE
TECHNICAL SERVICE PARTS LIST

ITEM NO.	DESCRIPTION	PART NUMBER	QUANTITY
201	Adapter Motor	702082	1
208	Worm Patt Actuator	785021	1
209	Housing	115758	1
212	O-Ring	757250	1
214	O-Ring	757077	1
216	Sleeve	115434	1
218	Swivel	104737	1
219	Gasket	714023	1
220	Brass Ball 1/4"	703017	53
221	Swivel Plug	742023	1
222	Roll Pin	744266	1
223	Hex Nut	734099	1
224	Throat	115757	1
232	Ball	704018	24
233	O-Ring	757048	1
234	Guide Tube	718182	1
235	O-Ring	757293	1
236	Piston Actuator	702076	1
237	Screw	767136	1
238	O-Ring	757055	1
240	Socket Head Screw	765134	1
241	Gear Ballscrew	718191	1
242	Hex Nut	734061	1
243	Socket Head Screw	763038	4
247	Socket Head Cap Screw	767086	2
248	Vent Breather	779078	2
249	Lanyard	729117	1
250	Roll Pin	741061	1
251	Bolt Drive	703487	1
253	Phillips Screw	763067	1
254	Handle	721321	1
255	Brake Handle	721320	1
257	Socket Head Cap Screw	767029	1
258	Baffle Cup	707370	1
259	Baffle Collar	707376	1
260	Threaded Stem	769508	1
261	Baffle Stop	768284	1
262	O-Ring	757045	1
263	Socket Head Set Screw	765076	1
264	Plate Identification	742122	1
265	Nail Grip	736045	4
270	Socket Head Cap Screw	4	
270	Socket Head Cap Screw	4	
271	O-Ring	757317	1
272	Motor 12V	731067	1
273	Shrink Cap	707125	1
274	O-Ring	757318	1
275	Spacer O-Ring	768258	1
276	O-Ring	757180	1
278	Gasket	716047	1
286	Spring	768288	1
287	Nut Cap	735056	1
288	Allen Head Screw	765008	1
289	Socket Head Set Screw	1	



Tested... Proven... Trusted.

ISO 9001 REGISTERED COMPANY

PHONE: 330.264.5678 or 800.228.1161 | FAX: 330.264.2944 or 800.531.7335 | akronbrass.com

REVISED: 7/11

WARRANTY AND DISCLAIMER: We warrant Akron Brass products for a period of five (5) years after purchase against defects in materials or workmanship. Akron Brass will repair or replace product which fails to satisfy this warranty. Repair or replacement shall be at the discretion of Akron Brass. Products must be promptly returned to Akron Brass for warranty service.

We will not be responsible for: wear and tear; any improper installation, use, maintenance or storage; negligence of the owner or user; repair or modification after delivery; damage; failure to follow our instructions or recommendations; or anything else beyond our control. WE MAKE NO WARRANTIES, EXPRESS OR IMPLIED, OTHER THAN THOSE INCLUDED IN THIS WARRANTY STATEMENT, AND WE DISCLAIM ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE. Further, we will not be responsible for any consequential, incidental or indirect damages (including, but not limited to, any loss of profits) from any cause whatsoever. No person has authority to change this warranty.

© Akron Brass Company. 2011 All rights reserved. No portion of this can be reproduced without the express written consent of Akron Brass Company.